

# Solve Your Screening and Grading Problems with the **GALAXY Sivtek Separator**

The Galaxy SIVTEK Separator range is engineered using the latest design techniques to give optimum performance in handling a wide range of products in a diverse range of industries.

Also Available as per  
cGMP Norms



Effective separation for high quality product

- # Accurate grading of different size particles

Provides optimum efficiency

- # Machine can be finely tuned by easy adjustment of out of balance weight system to maximise output
- # Provides up to five separations in a single operation to give maximum capacity
- # Multiple discharge outlets available for handling higher discharge rates

User friendly


- # Very easy to operate
- # Automatic discharge of material
- # Quick change clamping mechanism
- # Available with clean in place systems
- # Quick mesh change system

Reduces your maintenance costs and downtime

- # Manufactured to the highest quality standards
- # Low power consumption
- # Dependable motor with external lubricating system



[www.galaxysivtek.com](http://www.galaxysivtek.com)  
ISO 9001 : 2008



## Six Standard sizes to meet your sieving and separation needs

# The Galaxy SIVTEK Separator is manufactured in six standard sizes to match the requirements of a diverse range of applications and throughput rates: 24"(600mm), 30"(750mm), 40"(1000mm), 48"(1200mm), 60"(1500mm) and 72"(1800mm) diameter.

### Mesh Cleaning Options:

#### # Ball Tray

Anti blinding Ball Tray Arrangement, comprising of a coarse mesh beneath the sizing mesh on which a sufficient number of elastomer or polymer balls are placed to continuously tap the sizing screen. Continuous tapping dislodges the clogged particles from the sizing screen.

#### # Ring Tray

Ring Tray prevents screen blinding and stapling of the mesh. The action of the vibration causes sharp-edged sliding cylinders to scrape the underside of the screen, cutting off dangling fibrous material as well as freeing near-size material lodged in the openings.

**Always ask for authentic Galaxy SIVTEK® After Sales parts to keep your machines running to maximise your production.**

### Proven Screening and Grading technology

# Over 20 years of experience of solving customer problems is at your disposal to ensure the SIVTEK® Separators deliver the highest standards of operating performance and reliability.

### Established Industry Applications

Paper	Ceramics	Sugar
Food	Minerals	Chemicals
Polymers	Carbon / Coal	Pharmaceuticals

Visit our website [www.galaxysivtek.com](http://www.galaxysivtek.com) to find out how the Tetra SIVTEK™ can assist in overcoming your screening and separation problems to maximise the performance of your plant.

## GALAXY SIVTEK PVT. LTD.

Plot No.: 1406, GIDC, Waghodia-391760,  
Dist: Vadodara, Gujarat, India  
Ph: +91 2668 262 970; Fax: +91 2668 262 570  
Cell: +91 922 744 1206  
Email: [overseas@galaxysivtek.com](mailto:overseas@galaxysivtek.com)



[www.galaxysivtek.com](http://www.galaxysivtek.com)