

# ROTEX<sup>®</sup> MEGATEX XD<sup>™</sup>

*Smart Solutions For High Capacity Screening*

Web: [www.rotex.com](http://www.rotex.com)

The new and improved ROTEX<sup>®</sup> MEGATEX XD<sup>™</sup> was specifically designed to meet the demanding screening requirements of applications requiring high-capacity throughput. The MEGATEX XD provides unsurpassed screening performance when sharp separations and high efficiencies are required. The MEGATEX XD is able to maximize product recoveries at material temperatures up to 400° F (205° C).




## Superior Performance

- Higher capacity (25-50%) per square foot of screen cloth in a compact footprint.
- Screen deck slope of 6° to meet demanding product specifications and maximize screen efficiency.
- External drive cartridge allows continuous operation up to 400° F (205° C).
- Stainless steel or abrasion resistant steel construction and 'rockbox' landing areas for continuous impact on high-wear surfaces available.
- Single or double inlet plenum options with sliding inlet connections with long life Teflon<sup>™</sup> wear rings.

The unique elliptical-linear motion of the MEGATEX XD provides unsurpassed screening performance through:

- Equal feed distribution to all screen decks
- Uniform bed depth across entire screen surface
- Aggressive blinding control with durable mesh cleaning balls
- Excellent spreading and stratification



Quick opening discharge door provides access to each individual screen deck for inspection or change out.



### Discharge System

- Unique sleeveless brush system and discharge vent connection for added dust control without connecting sleeves.



### Patented Cam Lift Rail

- Internal lining rails with patented Lift-Rail system with non-binding stainless steel cam activation for easy screen frame installation and removal.





### Universal Sealing System

- Newly developed silicone D seals with easy press fit (no adhesives) for exceptional sealing between screen decks for fine separation.

## Drive & Suspension

- Easily accessible external drive.
- Single reaction cartridge with two spherical roller bearings—designed for 200,000 hours of service.
- Support shaft suspension system with industrial U-joint bearings and no maintenance, low, torsion center springs.
- Optional floor mounted suspension stand for installations without overhead support.



▼ Drive located externally in rear of MEGATEX.

## Single Screen Access

Stacked multiple deck, tray-access design allows individual screen access without the need to remove all decks. Single deck screen change in 10 minutes. All 12 decks in 2 hours.

## The Smart Solution

The ROTEX® MEGATEX XD™ is ideal for applications that require high capacity throughput.



© 2008 ROTEX Global, LLC

# ROTEX®

[www.rotex.com](http://www.rotex.com)

**Global Headquarters**  
1230 Knowlton Street  
Cincinnati, OH 45223  
T: (513) 541-1236  
F: (513) 541-4888  
E: [info@rotex.com](mailto:info@rotex.com)

**United Kingdom**  
Aston Lane North, Whitehouse Vale  
Runcorn, Cheshire WA7 3FA  
T: +44 (0) 192 870 61 00  
F: +44 (0) 192 870 61 19  
E: [sales@rotexeuropa.com](mailto:sales@rotexeuropa.com)

**Belgium**  
Avenue Lavoisier, 18B  
1300, Wavre  
T: +32 (0) 10 41 61 71  
F: +32 (0) 10 41 41 28  
E: [info@rotexeuropa.be](mailto:info@rotexeuropa.be)

**France**  
2 Avenue du Marechal Leclerc  
F-59110 La Madeleine  
T: +33 (0) 320 15 20 83  
F: +33 (0) 320 15 20 83  
E: [othouvard@rotex.com](mailto:othouvard@rotex.com)

**Germany**  
Technologie Fabrik Remscheid  
Berghäuser Str. 62  
D-42859 Remscheid  
T: +49 (0) 2191 89 06 25  
F: +49 (0) 2191 89 06 26  
E: [fspanknebel@rotex.com](mailto:fspanknebel@rotex.com)

**Benelux**  
Maldegemstraat 41  
7641 DX WIERDEN  
The Netherlands  
T: +31 (0) 546 57 91 31  
F: +31 (0) 546 57 91 31  
E: [fholle@rotex.com](mailto:fholle@rotex.com)

 Find your local representative online at [rotex.com/refinder](http://rotex.com/refinder)